

ISOLATION GOWN LEVEL 2 (10/PK)

MZH-209

- Comfortable, strong & durable SMS material for demanding situations.
- Best for: patient contact, decontamination, general clean-up House wide, med surg, icu
- 35 GSM
- Non-sterile
- Tie neck closure
- Tie waist
- One layer non-woven spunbond SMS



ANSI/AAMI PB70 BARRIER PERFORMANCE	AAMI Level 2
TEST METHOD	Water resistance: Impact penetration AATCC 42 Water resistance: Hydrostatic pressure AATCC 27
TEST DEFINITION	AATCC 42 Measures the resistance of fabrics to the liquid penetration of water by impact AATCC 127 Measures the resistance of fabrics to the liquid penetration of water by impact under constant & increasing hydrostatic pressure
REQUIREMENT	Spray impact < 1.0 g Hydrostatic pressure > 20 cm
ANTICIPATED FLUID EXPOSURE	Low fluid levels

LEVEL GUIDE			
1	2	3	4
Minimal Protection	Low Protection	Moderate Protection	High Protection

Contact your sales rep for more information or to place an order.